

NUOVA MAPA

400-02630 - Nuova Mapa 90° Table Leg - Silver Anodised. # 0612100

(Translated Instructions)



ASSEMBLY INSTRUCTIONS FOR WALL-MOUNTED ALUMINUM TABLE SUPPORT

Package Contents



1. 2 x BLACK CAPS for Guide
2. TABLE SUPPORT ARM – Square Tubular Aluminum, Silver Anodised, Complete with Grey Plate for Fixing the Table Top (not included)
3. TABLE SUPPORT TUBE & SLIDE BRACKET – Round Aluminum Tube, Silver Anodized, Complete with Gray Bracket with Aluminum Knob and Guide

Assembly Instructions:


Grasp the round aluminum tube 1. Loosen the plastic knob and pull the round tube with grey bracket out of the aluminum guide



In order to achieve a good rigidity of the table support, it is very important that the point where the guide is applied is particularly robust; If it is not, it is recommended to reinforce it by adding an additional wooden panel.



The guide should be applied at a height from the ground (measured from the centre of the rail to the floor of the vehicle) of about 28cm, keeping it exactly vertical with respect to the floor



If you are of the position of the rail, it is advisable to apply a light layer of adhesive sealant between the rail and the furniture in order to reinforce its seal.

1. Proceed by screwing the guide to the cabinet/wall, starting from the central hole. Use a screw with a diameter of no more than 4mm, and of a length appropriate to the thickness of the wood in which the guide is to be screwed.
2. Make sure the fence is in an upright position (90° to the floor). Insert the black cap with a hole in the lower part of the guide, and proceed by screwing on the lower part. Use a screw with a head diameter of no more than 7.5mm, with a screw diameter of no more than 4mm

and of a length appropriate to the thickness of the wood into which the guide is to be screwed.

3. Proceed by screwing on the upper part of the guide. Use a screw with a diameter of no more than 4mm and a length appropriate to the thickness of the wood into which the guide is to be screwed.
4. Insert the hose with the bracket into the previously mounted rail



5. Tighten the black knob in the desired position and insert the black top cap without hole into the guide.
6. Screw the table support plate to a previously prepared table top (not supplied). Use screws of appropriate length for the thickness of the table top.



7. Loosen the knob in the square tubular



8. Insert the tubular with plastic bushing, into the upper part of the round tube up to the set screw



9. Tighten the black knob to lock it

- If one of the two rotational movements of the upper part is difficult or noisy even when the knob is loose, the part can be lubricated with silicon spray.
- If you want to use the table in several positions inside the vehicle you can purchase additional optional aluminum rails with caps (400-02632 - Nuova Mapa Additional Alum Mounting Guide Kit for 90° Table Leg. # 0612150) to be fixed in other points of the vehicle.
- By loosening the various knobs, it is possible to rotate or remove the various parts and store everything in a stowage compartment leaving only the guide attached to the vehicle

Thank you for purchasing the Nuova Mapa 90° Table Leg



Proudly distributed in Australia & New Zealand by Coast to Coast RV Services

www.coastrv.com.au